


RackPower iPDU, RP1326, 100-240 VAC, 1-phase

Servicios públicos de energía

NÚMERO DE CATÁLOGO

RP1326



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

CARACTERÍSTICAS

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 100 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13, C19 outlets

ATRIBUTOS DEL PRODUCTO

Product Type: Socket Strip

Socket Type: IEC C13; IEC C19

Color: Negro

Length: 1490 mm

Voltage AC: 208 V

Function: Input Monitored

Profundidad: 53 mm

Ancho: 52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE