

RackPower Single Temperature and Humidity Sensor

Servicios públicos de energía

NÚMERO DE CATÁLOGO

EA9103



Single Temperature and Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

CARACTERÍSTICAS

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy $\pm 2\%$

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy $\pm 5\%$

ATRIBUTOS DEL PRODUCTO

Product Type: Sensor

Type: Temperature and Humidity

Works With: RackPower

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento

completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE