

# Front Panel, Anodized With Untreated Edges, Unshielded

## Servicios públicos de energía

Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.



### CERTIFICACIONES



### CARACTERÍSTICAS

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

### ESPECIFICACIONES

Table 1/3

| Número de catálogo | Rack Height | Rack Width | Package Quantity | Handle Type | Montaje        | Front Finish |
|--------------------|-------------|------------|------------------|-------------|----------------|--------------|
| 30818-271          | 2 U         | 84 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-310          | 3 U         | 42 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |

| Número de catálogo | Rack Height | Rack Width | Package Quantity | Handle Type | Montaje        | Front Finish |
|--------------------|-------------|------------|------------------|-------------|----------------|--------------|
| 30818-331          | 3 U         | 63 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-352          | 3 U         | 84 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-434          | 4 U         | 84 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-556          | 6 U         | 42 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-577          | 6 U         | 63 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-598          | 6 U         | 84 HP      | 1                | Ninguno     | Screw-on Front | Anodizado    |
| 30810-433          | 3 U         | 2 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-747          | 6 U         | 2 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-272          | 3 U         | 3 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-273          | 3 U         | 4 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-274          | 3 U         | 5 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-275          | 3 U         | 6 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-276          | 3 U         | 7 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-277          | 3 U         | 8 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-279          | 3 U         | 10 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-281          | 3 U         | 12 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-282          | 3 U         | 14 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-289          | 3 U         | 21 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |

| Número de catálogo | Rack Height | Rack Width | Package Quantity | Handle Type | Montaje        | Front Finish |
|--------------------|-------------|------------|------------------|-------------|----------------|--------------|
| 30818-296          | 3 U         | 28 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-518          | 6 U         | 4 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-519          | 6 U         | 5 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-520          | 6 U         | 6 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-521          | 6 U         | 7 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-522          | 6 U         | 8 HP       | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-524          | 6 U         | 10 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-526          | 6 U         | 12 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-528          | 6 U         | 14 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-530          | 6 U         | 16 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-535          | 6 U         | 21 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |
| 30818-542          | 6 U         | 28 HP      | 5                | Ninguno     | Screw-on Front | Anodizado    |

Table 2/3

| Número de catálogo | Rear Finish | Treated Edges | Cumple con                      | EMC Shielding | Altura   | Material |
|--------------------|-------------|---------------|---------------------------------|---------------|----------|----------|
| 30818-271          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 84 mm    | Aluminio |
| 30818-310          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-331          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |

| Número de catálogo | Rear Finish | Treated Edges | Cumple con                      | EMC Shielding | Altura   | Material |
|--------------------|-------------|---------------|---------------------------------|---------------|----------|----------|
| 30818-352          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-434          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 172.9 mm | Aluminio |
| 30818-556          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-577          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-598          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30810-433          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-747          | Anodizado   | Sí            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-272          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-273          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-274          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-275          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-276          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-277          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-279          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |

| Número de catálogo | Rear Finish | Treated Edges | Cumple con                      | EMC Shielding | Altura   | Material |
|--------------------|-------------|---------------|---------------------------------|---------------|----------|----------|
| 30818-281          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-282          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-289          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-296          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminio |
| 30818-518          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-519          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-520          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-521          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-522          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-524          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-526          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-528          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-530          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |
| 30818-535          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |

| Número de catálogo | Rear Finish | Treated Edges | Cumple con                      | EMC Shielding | Altura   | Material |
|--------------------|-------------|---------------|---------------------------------|---------------|----------|----------|
| 30818-542          | Anodizado   | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminio |

Table 3/3

| Número de catálogo | Product Type | Tipo                       | Ancho    |
|--------------------|--------------|----------------------------|----------|
| 30818-271          | Front Panel  | Front Panel without Handle | 426.4 mm |
| 30818-310          | Front Panel  | Front Panel without Handle | 213 mm   |
| 30818-331          | Front Panel  | Front Panel without Handle | 319.7 mm |
| 30818-352          | Front Panel  | Front Panel without Handle | 426.4 mm |
| 30818-434          | Front Panel  | Front Panel without Handle | 426.4 mm |
| 30818-556          | Front Panel  | Front Panel without Handle | 213 mm   |
| 30818-577          | Front Panel  | Front Panel without Handle | 319.7 mm |
| 30818-598          | Front Panel  | Front Panel without Handle | 426.4 mm |
| 30810-433          | Front Panel  | Front Panel without Handle | 9.8 mm   |
| 30818-747          | Front Panel  | Front Panel without Handle | 9.8 mm   |
| 30818-272          | Front Panel  | Front Panel without Handle | 14.9 mm  |
| 30818-273          | Front Panel  | Front Panel without Handle | 20 mm    |
| 30818-274          | Front Panel  | Front Panel without Handle | 25 mm    |
| 30818-275          | Front Panel  | Front Panel without Handle | 30.1 mm  |
| 30818-276          | Front Panel  | Front Panel without Handle | 35.2 mm  |

| Número de catálogo | Product Type | Tipo                       | Ancho    |
|--------------------|--------------|----------------------------|----------|
| 30818-277          | Front Panel  | Front Panel without Handle | 40.3 mm  |
| 30818-279          | Front Panel  | Front Panel without Handle | 50.5 mm  |
| 30818-281          | Front Panel  | Front Panel without Handle | 60.6 mm  |
| 30818-282          | Front Panel  | Front Panel without Handle | 70.8 mm  |
| 30818-289          | Front Panel  | Front Panel without Handle | 106.3 mm |
| 30818-296          | Front Panel  | Front Panel without Handle | 141.9 mm |
| 30818-518          | Front Panel  | Front Panel without Handle | 20 mm    |
| 30818-519          | Front Panel  | Front Panel without Handle | 25 mm    |
| 30818-520          | Front Panel  | Front Panel without Handle | 30.1 mm  |
| 30818-521          | Front Panel  | Front Panel without Handle | 35.2 mm  |
| 30818-522          | Front Panel  | Front Panel without Handle | 40.3 mm  |
| 30818-524          | Front Panel  | Front Panel without Handle | 50.5 mm  |
| 30818-526          | Front Panel  | Front Panel without Handle | 60.6 mm  |
| 30818-528          | Front Panel  | Front Panel without Handle | 70.8 mm  |
| 30818-530          | Front Panel  | Front Panel without Handle | 80.9 mm  |
| 30818-535          | Front Panel  | Front Panel without Handle | 106.3 mm |
| 30818-542          | Front Panel  | Front Panel without Handle | 141.9 mm |

## ADDITIONAL PRODUCT DETAILS

---

Please order fixing material (sleeves, collar screws) separately.

## ADVERTENCIA

---

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**