

Front Panel, Anodized With Untreated Edges, Unshielded

Servicios públicos de energía

Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.



CERTIFICACIONES



CARACTERÍSTICAS

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaje	Front Finish
30818-271	2 U	84 HP	1	Ninguno	Screw-on Front	Anodizado
30818-310	3 U	42 HP	1	Ninguno	Screw-on Front	Anodizado

Número de catálogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaje	Front Finish
30818-331	3 U	63 HP	1	Ninguno	Screw-on Front	Anodizado
30818-352	3 U	84 HP	1	Ninguno	Screw-on Front	Anodizado
30818-434	4 U	84 HP	1	Ninguno	Screw-on Front	Anodizado
30818-556	6 U	42 HP	1	Ninguno	Screw-on Front	Anodizado
30818-577	6 U	63 HP	1	Ninguno	Screw-on Front	Anodizado
30818-598	6 U	84 HP	1	Ninguno	Screw-on Front	Anodizado
30810-433	3 U	2 HP	5	Ninguno	Screw-on Front	Anodizado
30818-747	6 U	2 HP	5	Ninguno	Screw-on Front	Anodizado
30818-272	3 U	3 HP	5	Ninguno	Screw-on Front	Anodizado
30818-273	3 U	4 HP	5	Ninguno	Screw-on Front	Anodizado
30818-274	3 U	5 HP	5	Ninguno	Screw-on Front	Anodizado
30818-275	3 U	6 HP	5	Ninguno	Screw-on Front	Anodizado
30818-276	3 U	7 HP	5	Ninguno	Screw-on Front	Anodizado
30818-277	3 U	8 HP	5	Ninguno	Screw-on Front	Anodizado
30818-279	3 U	10 HP	5	Ninguno	Screw-on Front	Anodizado
30818-281	3 U	12 HP	5	Ninguno	Screw-on Front	Anodizado
30818-282	3 U	14 HP	5	Ninguno	Screw-on Front	Anodizado
30818-289	3 U	21 HP	5	Ninguno	Screw-on Front	Anodizado

Número de catálogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaje	Front Finish
30818-296	3 U	28 HP	5	Ninguno	Screw-on Front	Anodizado
30818-518	6 U	4 HP	5	Ninguno	Screw-on Front	Anodizado
30818-519	6 U	5 HP	5	Ninguno	Screw-on Front	Anodizado
30818-520	6 U	6 HP	5	Ninguno	Screw-on Front	Anodizado
30818-521	6 U	7 HP	5	Ninguno	Screw-on Front	Anodizado
30818-522	6 U	8 HP	5	Ninguno	Screw-on Front	Anodizado
30818-524	6 U	10 HP	5	Ninguno	Screw-on Front	Anodizado
30818-526	6 U	12 HP	5	Ninguno	Screw-on Front	Anodizado
30818-528	6 U	14 HP	5	Ninguno	Screw-on Front	Anodizado
30818-530	6 U	16 HP	5	Ninguno	Screw-on Front	Anodizado
30818-535	6 U	21 HP	5	Ninguno	Screw-on Front	Anodizado
30818-542	6 U	28 HP	5	Ninguno	Screw-on Front	Anodizado

Table 2/3

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30818-271	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminio
30818-310	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-331	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30818-352	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-434	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9 mm	Aluminio
30818-556	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-577	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-598	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30810-433	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-747	Anodizado	Sí	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-272	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-273	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-274	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-275	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-276	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-277	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-279	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30818-281	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-282	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-289	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-296	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminio
30818-518	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-519	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-520	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-521	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-522	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-524	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-526	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-528	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-530	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio
30818-535	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
30818-542	Anodizado	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminio

Table 3/3

Número de catálogo	Product Type	Tipo	Ancho
30818-271	Front Panel	Front Panel without Handle	426.4 mm
30818-310	Front Panel	Front Panel without Handle	213 mm
30818-331	Front Panel	Front Panel without Handle	319.7 mm
30818-352	Front Panel	Front Panel without Handle	426.4 mm
30818-434	Front Panel	Front Panel without Handle	426.4 mm
30818-556	Front Panel	Front Panel without Handle	213 mm
30818-577	Front Panel	Front Panel without Handle	319.7 mm
30818-598	Front Panel	Front Panel without Handle	426.4 mm
30810-433	Front Panel	Front Panel without Handle	9.8 mm
30818-747	Front Panel	Front Panel without Handle	9.8 mm
30818-272	Front Panel	Front Panel without Handle	14.9 mm
30818-273	Front Panel	Front Panel without Handle	20 mm
30818-274	Front Panel	Front Panel without Handle	25 mm
30818-275	Front Panel	Front Panel without Handle	30.1 mm
30818-276	Front Panel	Front Panel without Handle	35.2 mm

Número de catálogo	Product Type	Tipo	Ancho
30818-277	Front Panel	Front Panel without Handle	40.3 mm
30818-279	Front Panel	Front Panel without Handle	50.5 mm
30818-281	Front Panel	Front Panel without Handle	60.6 mm
30818-282	Front Panel	Front Panel without Handle	70.8 mm
30818-289	Front Panel	Front Panel without Handle	106.3 mm
30818-296	Front Panel	Front Panel without Handle	141.9 mm
30818-518	Front Panel	Front Panel without Handle	20 mm
30818-519	Front Panel	Front Panel without Handle	25 mm
30818-520	Front Panel	Front Panel without Handle	30.1 mm
30818-521	Front Panel	Front Panel without Handle	35.2 mm
30818-522	Front Panel	Front Panel without Handle	40.3 mm
30818-524	Front Panel	Front Panel without Handle	50.5 mm
30818-526	Front Panel	Front Panel without Handle	60.6 mm
30818-528	Front Panel	Front Panel without Handle	70.8 mm
30818-530	Front Panel	Front Panel without Handle	80.9 mm
30818-535	Front Panel	Front Panel without Handle	106.3 mm
30818-542	Front Panel	Front Panel without Handle	141.9 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE