

Single-Entry Power Connection with Junction Box



nVent RAYCHEM JBS-100 is a junction box used to connect power to one nVent RAYCHEM BTV, QTVR, XTVR, HTV or VPL industrial parallel heating cable. Offered in three versions, customized for local installation practices, each are also available with a power indicator. JBS-100-E, JBS-100-L-E; JBS-100-EP, JBS-100-L-EP; JBS-100-A, JBS-100-L-A.

CARACTERÍSTICAS

Simple and fast to install, spacious boxes with front access, captive lid screws and robust spring type terminals for secure fixing

Part of a modular component system, providing maximum flexibility

One range for all nVent RAYCHEM industrial parallel heating cables

Simplified design in hazardous area, integral part of system approval

Cold-applied: core sealing boot with non-curing sealant; no heat gun, no hot work permit needed

Reliable during long life: 10 year extended product warranty available, maintenance free

ESPECIFICACIONES

For Ex-Zone Gas:	1, 2
Inlet Quantity:	2
Connection Clamp Quantity:	3
Cable Entry:	3/4"
Max Conductor Cross Section:	10 mm ²
For Ex-Zone Dust:	21, 22
Profundidad:	90 mm
Ancho:	120 mm
Altura:	242 mm
Tipo de conexión:	Cold Applied
Material:	Glass Fiber Reinforced Polymer
Area Classification:	Non-Hazardous; Hazardous
Clasificación IP:	IP66

Knockouts Included:	No
Montaje:	On Pipe
Cover Attachment:	Screwed
Libre de halógenos:	Sí

Table 1/1

Número de catálogo	Nombre del artículo	Ambient Temperature	Light Indication Included	Earth Plate Included	Below Insulation
085947-000	JBS-100-A	-40 to 56 °C	No	No	No
944699-000	JBS-100-L-A	-40 to 40 °C	Sí	No	No
C26470-000	JBS-100-A6	-40 to 56 °C	No	No	No

ADDITIONAL PRODUCT DETAILS

Localized versions may exist with limited approvals and different part numbers. Contact your local sales representative.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT