

Serie T de gran capacidad para exteriores

Servicios públicos de energía



Los aires acondicionados de gran capacidad serie T mantienen baja la temperatura de los equipos, incluso con cargas de calor máximas. Su diseño discreto les permite adaptarse a los entornos exigentes de fábricas y espacios exteriores. Todas las unidades están equipadas con componentes resistentes a la corrosión, calentadores de compresor y controles de presión superior para obtener un rendimiento óptimo en exteriores.

INDUSTRY STANDARDS

CE

Listado en UL/cUL; Tipo 12, 3R, 4; 4X opcional; N.º de archivo SA6453

EAC

Telcordia GR-487 capable

CARACTERÍSTICAS

Compact footprint to minimize real estate and maximize capacity

Cleanable, reusable aluminum mesh filter protects coils for maximum cooling performance

R-407C refrigerant

Models for 230 and 460 VAC power input

Operating temperature range from -40 F/-40 C to 131 F/55 C

Reliable mechanical thermostat on enclosure side of the unit

Dual condenser-side air movers for performance redundancy

Painted galvanized sheet-metal cover for rugged factory and outdoor environments

Exterior and fully recessed mounting options on many models

Easy-mount flanges for simple installation

Every unit functionally tested before shipping

Standard Outdoor Air Conditioner models include telcordia GR-487 capable, thermostat, corrosion-resistant components, malfunction switch, compressor heater, head pressure control and enclosure heater

Mounting hardware, gaskets and user manual furnished with the unit

ESPECIFICACIONES

Espesor: 1,21 mm

Table 1/3

Número de catálogo	Número de artículo	Altura	Ancho	Profundidad	Tensión nominal	Control de acceso remoto
T622226G102	34958	1569 mm	506 mm	441 mm	230 V	No
T622226G150	23404	1569 mm	506 mm	441 mm	230 V	No
T622226G151	34961	1569 mm	506 mm	441 mm	230 V	No
T622246G400	19433	1569 mm	506 mm	441 mm	460 V	No
T703626G150	23407	1772 mm	579 mm	532 mm	230 V	No
T703646G400	24307	1772 mm	579 mm	532 mm	460 V	No
T706026G150	23413	1772 mm	911 mm	583 mm	230 V	No
T706046G400	26232	1772 mm	911 mm	583 mm	460 V	No

Table 2/3

Número de catálogo	Número de artículo	Number of Phases	Nominal Capacity Btu/h	Nominal Capacity Watts	Temperatura de funcionamiento	Max Current
T622226G102	34958	1	23500 Btu/h	6886 W	-40 to 55 °C	22 A
T622226G150	23404	1	23500 Btu/h	6886 W	-40 to 55 °C	22 A
T622226G151	34961	1	23500 Btu/h	6886 W	-40 to 55 °C	22 A
T622246G400	19433	1	23500 Btu/h	6886 W	-40 to 55 °C	12 A
T703626G150	23407	1	43000 Btu/h	12602 W	-40 to 55 °C	36 A
T703646G400	24307	1	43000 Btu/h	12602 W	-40 to 55 °C	18 A

Número de catálogo	Número de artículo	Number of Phases	Nominal Capacity Btu/h	Nominal Capacity Watts	Temperatura de funcionamiento	Max Current
T706026G150	23413	1	60000 Btu/h	17584 W	-40 to 50 °C	40 A
T706046G400	26232	1	60000 Btu/h	17584 W	-40 to 50 °C	15.3 A

Table 3/3

Número de catálogo	Número de artículo	Material	Acabado	Color	Color Code
T622226G102	34958	Stainless Steel 304	Brushed #3	Unpainted	
T622226G150	23404	Mild Steel	Recubrimiento de polvo	Light Gray	RAL 7035
T622226G151	34961	Stainless Steel 304	Brushed #3	Unpainted	
T622246G400	19433	Mild Steel	Recubrimiento de polvo	Light Gray	RAL 7035
T703626G150	23407	Mild Steel	Recubrimiento de polvo	Light Gray	RAL 7035
T703646G400	24307	Mild Steel	Recubrimiento de polvo	Light Gray	RAL 7035
T706026G150	23413	Mild Steel	Recubrimiento de polvo	Light Gray	RAL 7035
T706046G400	26232	Mild Steel	Recubrimiento de polvo	Light Gray	RAL 7035

ADDITIONAL PRODUCT DETAILS

* ProAir A/C may be more appropriate. Refer to ProAir A/C Chapter. Consult the Factory for availability and catalog number.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE