

# Modular Jumper Cable, Metal Connectors

nVent RAYCHEM TraceTek TT-MJC-XX is a range of jumper cables, with metal connectors, available in various fixed lengths.

## CARACTERÍSTICAS

Simple and fast to install, modular

Easy to design

## ESPECIFICACIONES

|                               |                                      |
|-------------------------------|--------------------------------------|
| <b>Core Quantity:</b>         | 4                                    |
| <b>Diámetro exterior:</b>     | 4,2 mm                               |
| <b>Tamaño del conductor:</b>  | 18 AWG                               |
| <b>Core Identification:</b>   | Color                                |
| <b>Material conductor:</b>    | Cobre                                |
| <b>Outer Sheath Material:</b> | ECTFE                                |
| <b>Material aislante:</b>     | Fluorinated Ethylene Propylene (FEP) |
| <b>Material del conector:</b> | metal                                |

Table 1/1

| Número de catálogo | Nombre del artículo     | Longitud | Color        |
|--------------------|-------------------------|----------|--------------|
| 013247-000         | TT-MJC-1M/3FT-MC        | 1 m      | Clear Jacket |
| 057111-000         | TT-MJC-15M/50FT-MC      | 15 m     | Clear Jacket |
| 078783-000         | TT-MJC-3M/10FT-MC       | 3 m      | Clear Jacket |
| 169643-000         | TT-MJC-7.5M/25FT-MC     | 7.5 m    | Clear Jacket |
| 935637-000         | TT-MJC-30M/100FT-MC     | 30 m     | Clear Jacket |
| 664356-000         | TT-MJC-30M/100FT-MC-BLK | 30 m     | Negro        |
| 678452-000         | TT-MJC-15M/50FT-MC-BLK  | 15 m     | Negro        |

| Número de catálogo | Nombre del artículo     | Longitud | Color |
|--------------------|-------------------------|----------|-------|
| 693994-000         | TT-MJC-7.5M/25FT-MC-BLK | 7.5 m    | Negro |
| 709898-000         | TT-MJC-3M/10FT-MC-BLK   | 3 m      | Negro |
| 726164-000         | TT-MJC-1M/3FT-MC-BLK    | 1 m      | Negro |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

### Norteamérica

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latinoamérica

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**