


Front Panel, Shielded, Bottom Hinged

Servicios públicos de energía

U-profile front panel bottom hinged for textile gasket.



CERTIFICACIONES



CARACTERÍSTICAS

U-profile front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

Shielded, U front panel with textile EMC gasket

Suitable for sub racks (EuropacPRO) and cases (RatiopacPRO, PropacPRO, CompacPRO)

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Rack Width	Package Quantity	Montaje	EMC Gasket Type	Front Finish
20848-599	3 U	42 HP	1	Hinged, Bottom	Textile	Anodizado
20848-600	3 U	63 HP	1	Hinged, Bottom	Textile	Anodizado

Número de catálogo	Rack Height	Rack Width	Package Quantity	Montaje	EMC Gasket Type	Front Finish
20848-601	3 U	84 HP	1	Hinged, Bottom	Textile	Anodizado
20848-602	6 U	42 HP	1	Hinged, Bottom	Textile	Anodizado
20848-603	6 U	63 HP	1	Hinged, Bottom	Textile	Anodizado
20848-604	6 U	84 HP	1	Hinged, Bottom	Textile	Anodizado
20848-605	4 U	42 HP	1	Hinged, Bottom	Textile	Anodizado
20848-606	4 U	63 HP	1	Hinged, Bottom	Textile	Anodizado
20848-607	4 U	84 HP	1	Hinged, Bottom	Textile	Anodizado
20848-608	3 U	28 HP	1	Hinged, Bottom	Textile	Anodizado
20848-696	6 U	28 HP	1	Hinged, Bottom	Textile	Anodizado

Table 2/3

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
20848-599	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-600	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-601	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-602	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-603	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio
20848-604	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio

Número de catálogo	Rear Finish	Treated Edges	Cumple con	EMC Shielding	Altura	Material
20848-605	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminio
20848-606	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminio
20848-607	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminio
20848-608	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminio
20848-696	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminio

Table 3/3

Número de catálogo	Product Type	Tipo	Ancho
20848-599	Front Panel	Front Panel without Handle	213 mm
20848-600	Front Panel	Front Panel without Handle	319.7 mm
20848-601	Front Panel	Front Panel without Handle	426.4 mm
20848-602	Front Panel	Front Panel without Handle	213 mm
20848-603	Front Panel	Front Panel without Handle	319.7 mm
20848-604	Front Panel	Front Panel without Handle	426.4 mm
20848-605	Front Panel	Front Panel without Handle	213 mm
20848-606	Front Panel	Front Panel without Handle	319.7 mm
20848-607	Front Panel	Front Panel without Handle	426.4 mm
20848-608	Front Panel	Front Panel without Handle	141.9 mm

Número de catálogo	Product Type	Tipo	Ancho
20848-696	Front Panel	Front Panel without Handle	141.9 mm

ADDITIONAL PRODUCT DETAILS

Front panel can be removed in opened position (> 135°).

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE