


# Joint Bond Mold Pair Only, Signal, 85-141 lb T-Rail, 1" Tab Bond Terminal Style, Mold and Mold Cleaning Tool, 5/16" Bondstrand

## Data Solutions

### CATALOG NUMBER

**SBS898**



### FEATURES

Pair of replacement molds designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

### PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: 1" Tab

Product: Mold and Mold Cleaning Tool

Conductor Size: 5/16" Bondstrand

Conductor Outer Diameter, Nominal: 7.94mm

Welder Style: T6; T7

Mold Only: No

Welding Material: SB32 x 2, Sold Separately

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**