

Crimping Compression Tool, Battery Powered



FEATURES

Wide cross section range

Ergonomic design

High-performance 18 volt lithium-ion battery for increased work capacity

Automatic retraction stop (ARS) after completed crimping

Lightweight and easy to use

Includes easy-to-carry custom case

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Applied Force	System	Dies	Crimping Shape	Conductor Size
MLB	716920	50kN	Battery-powered hydraulic	RKML series, PKML series	Hexagon	#10 Stranded - 500 kcmil Stranded, 6 mm ² Stranded - 240 mm ² Stranded
M3B	716915	120kN	Battery-powered hydraulic	RKM3 series, PKM3 series	Hexagon	#6 Stranded - 800 kcmil Stranded, 16 mm ² Stranded - 400 mm ² Stranded

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE