

Vaihtolaippa | Seinäkotelot, AFA

This gland plate allows for mounting FL21 gland plates, commonly used in Scandinavia.



FEATURES

Description: Adapts FL gland plates to the wall mounted, steel enclosures gland opening.

Material: 1.4 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness: 1.4mm
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	Height	Width	Depth	FL Opening Quantity	Gland Plate Type	Gland Plate Opening Width
AFA01R5	2mm	242mm	128mm	1	1, FL13	210mm
AFA04R5	2mm	542mm	128mm	2	4, FL21	510mm
AFA03R5	2mm	442mm	128mm	1	3, FL21	410mm
AFA02R5	2mm	342mm	128mm	1	2, FL21	310mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE