

Sokkelin etu- ja takaosa | Seinäkotelot, P



This plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

FEATURES

Description: Four corner pieces with removable front covers. The side panels PA must be ordered separately. Available heights: 100 and 200 mm. Machining is required.

Material: 2.5 mm mild steel for corner pieces and 1.5 mm mild steel for covers.

Finish: RAL 7022 structured powder coating.

Pack quantity: 4 corner pieces and 2 front covers, with mounting accessories.

SPECIFICATIONS

Thickness: 1.5mm
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7022
Color: Umbra Gray

Table 1/1

Catalog Number	Height	Width	Depth	Compatible Enclosure Width	Enclosure Material	Product Family
P1080	100mm	793mm	95mm	800mm	Mild Steel	Wall Mounted
P2080	200mm	793mm	95mm	800mm	Mild Steel	Wall Mounted
P1120	100mm	1193mm	95mm	1200mm	Mild Steel	Wall Mounted
P2120	200mm	1193mm	95mm	1200mm	Mild Steel	Wall Mounted
P1100	100mm	993mm	95mm	1000mm	Mild Steel	Wall Mounted
P2100	200mm	993mm	95mm	1000mm	Mild Steel	Wall Mounted
P1060	100mm	593mm	95mm	600mm	Mild Steel	Wall Mounted
P2060	200mm	593mm	95mm	600mm	Mild Steel	Wall Mounted
P1040	100mm	393mm	95mm	400mm	Mild Steel	Wall Mounted
P2040	200mm	393mm	95mm	400mm	Mild Steel	Wall Mounted
P1050	100mm	493mm	95mm	500mm	Mild Steel	Wall Mounted
P2050	200mm	493mm	95mm	500mm	Mild Steel	Wall Mounted

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE