

# Asennuslevy | Lattiakaapit, MP



The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.

## FEATURES

Description: Standard mounting plate. It can also be mounted on the side of an enclosure by using MPS kit or slid in from the side with the MTS profile. For heavy loads in vibrating environments use mounting plate reinforcement profile MPR and MPE or MPEF brackets.

Material: 3 mm galvanized steel.

Pack quantity: 1 piece.

Maximum load: 6000 N.

Mounting requirements: Use MPA for mounting the MP inside the enclosure. Adjustable in depth with MPD accessory.

## SPECIFICATIONS

**Thickness:** 3mm  
**Finish:** Galvanized  
**Material:** Mild Steel

Table 1/1

| Catalog Number | Height | Width  | Depth | Mounting Plate Height | Mounting Plate Width |
|----------------|--------|--------|-------|-----------------------|----------------------|
| MP1606         | 1600mm | 600mm  | 25mm  | 1494mm                | 494mm                |
| MP1608         | 1600mm | 800mm  | 25mm  | 1494mm                | 694mm                |
| MP1806         | 1800mm | 600mm  | 25mm  | 1694mm                | 494mm                |
| MP1808         | 1800mm | 800mm  | 25mm  | 1694mm                | 694mm                |
| MP2006         | 2000mm | 600mm  | 25mm  | 1894mm                | 494mm                |
| MP2008         | 2000mm | 800mm  | 25mm  | 1894mm                | 694mm                |
| MP1212         | 1200mm | 1200mm | 25mm  | 1094mm                | 1094mm               |
| MP1612         | 1600mm | 1200mm | 25mm  | 1494mm                | 1094mm               |
| MP1812         | 1800mm | 1200mm | 25mm  | 1694mm                | 1094mm               |
| MP1816         | 1800mm | 1600mm | 25mm  | 1694mm                | 1494mm               |
| MP2012         | 2000mm | 1200mm | 25mm  | 1894mm                | 1094mm               |
| MP2016         | 2000mm | 1600mm | 25mm  | 1894mm                | 1494mm               |
| MP1206         | 1200mm | 600mm  | 25mm  | 1094mm                | 494mm                |
| MP1208         | 1200mm | 800mm  | 25mm  | 1094mm                | 694mm                |
| MP1406         | 1400mm | 600mm  | 25mm  | 1294mm                | 494mm                |
| MP1408         | 1400mm | 800mm  | 25mm  | 1294mm                | 694mm                |

| Catalog Number | Height | Width  | Depth | Mounting Plate Height | Mounting Plate Width |
|----------------|--------|--------|-------|-----------------------|----------------------|
| MP1610         | 1600mm | 1000mm | 25mm  | 1494mm                | 894mm                |
| MP1810         | 1800mm | 1000mm | 25mm  | 1694mm                | 894mm                |
| MP2010         | 2000mm | 1000mm | 25mm  | 1894mm                | 894mm                |
| MP2210         | 2200mm | 1000mm | 25mm  | 2094mm                | 894mm                |
| MP2212         | 2200mm | 1200mm | 25mm  | 2094mm                | 1094mm               |
| MP1804         | 1800mm | 400mm  | 25mm  | 1694mm                | 294mm                |
| MP1805         | 1800mm | 500mm  | 25mm  | 1694mm                | 394mm                |
| MP2004         | 2000mm | 400mm  | 25mm  | 1894mm                | 294mm                |
| MP2005         | 2000mm | 500mm  | 25mm  | 1894mm                | 394mm                |
| MP2206         | 2200mm | 600mm  | 25mm  | 2094mm                | 494mm                |
| MP2208         | 2200mm | 800mm  | 25mm  | 2094mm                | 694mm                |
| MP1410         | 1400mm | 1000mm | 25mm  | 1294mm                | 894mm                |
| MP1412         | 1400mm | 1200mm | 25mm  | 1294mm                | 1094mm               |

## ADDITIONAL PRODUCT DETAILS

Note: for 1600 mm width, the mounting plate is delivered as two 800 mm width mounting plates and one filler plate.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**