

NH-kuormaerotin ja varokkeet



Snap-action switch enables safe operator-independent switching.

FEATURES

Description: 3-pole NH switch disconnecter with fuses. With multifunction handle (snap action switch mechanism).
Connection at the bottom.

Rated voltage: 690 V

For busbars: 12, 15, 20, 25, 30 × 5, 10

Power dissipation at 80% load: 18.6 W(33500), 52.5 W (33510)

Pack quantity: 1 pc.

Approvals: IEC, VDE, DNV GL

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Enclosure Material	Product Family	Material	Finish
33500	200mm	106mm	Plastic	IEC General Accessories	Plastic	Smooth
33510	286mm	184mm	Plastic	IEC General Accessories	Plastic	Smooth

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE