

Conduit System for Parallel Heating Cables



nVent RAYCHEM CCON25 series are conduit systems for additional mechanical protection when using off-pipe mounted junction boxes.

FEATURES

Simple and fast to install

Available in different materials, for different temperatures

Excellent mechanical protection

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Cable Type: For Parallel Heaters

Outdoor Installation: Yes

Table 1/1

Catalog Number	Item Name	E-Number	Material	Outer Diameter	Operating Temperature
1244-003280	CCON25-CMT-25M	1114501	Modified Polyamide	28.5 mm	-40 to 135 °C
1244-003281	CCON25-CMT-2M	1114500	Modified Polyamide	28.5 mm	-40 to 135 °C
1244-003474	CCON25-CMT/HT-1.67/0.33M	1114504	Modified Polyamide	28.8 mm	-40 to 135 °C
1244-003284	CCON25-CHT-2M	1114502	PFA	28.8 mm	-200 to 260 °C
1244-003283	CCON25-CHT-25M	1114503	PFA	28.8 mm	-200 to 260 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT