


# DIN Rail

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



## FEATURES

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

## SPECIFICATIONS

**Product Type:** DIN Rail

Table 1/2

| Catalog Number | Material | Height | Length | Finish      | Package Quantity | Depth |
|----------------|----------|--------|--------|-------------|------------------|-------|
| 20118-878      | Steel    | 35mm   | 125mm  | Zinc Plated | 4                | 7.5mm |
| 20118-879      | Steel    | 35mm   | 175mm  | Zinc Plated | 4                | 7.5mm |
| 20118-872      | Steel    | 35mm   | 125mm  | Zinc Plated | 4                | 15mm  |
| 20118-880      | Steel    | 35mm   | 275mm  | Zinc Plated | 4                | 7.5mm |
| 20118-890      | Steel    | 35mm   | 125mm  | Zinc Plated | 10               | 7.5mm |
| 20118-873      | Steel    | 35mm   | 175mm  | Zinc Plated | 4                | 15mm  |

| CatalogNumber | Material | Height | Length | Finish      | Package Quantity | Depth |
|---------------|----------|--------|--------|-------------|------------------|-------|
| 20118-881     | Steel    | 35mm   | 375mm  | Zinc Plated | 4                | 7.5mm |
| 20118-891     | Steel    | 35mm   | 175mm  | Zinc Plated | 10               | 7.5mm |
| 20118-882     | Steel    | 35mm   | 475mm  | Zinc Plated | 4                | 7.5mm |
| 20118-874     | Steel    | 35mm   | 275mm  | Zinc Plated | 4                | 15mm  |
| 20118-884     | Steel    | 35mm   | 125mm  | Zinc Plated | 10               | 15mm  |
| 20118-883     | Steel    | 35mm   | 575mm  | Zinc Plated | 4                | 7.5mm |
| 20118-892     | Steel    | 35mm   | 275mm  | Zinc Plated | 10               | 7.5mm |
| 20118-875     | Steel    | 35mm   | 375mm  | Zinc Plated | 4                | 15mm  |
| 20118-885     | Steel    | 35mm   | 175mm  | Zinc Plated | 10               | 15mm  |
| 20118-876     | Steel    | 35mm   | 475mm  | Zinc Plated | 4                | 15mm  |
| 20118-893     | Steel    | 35mm   | 375mm  | Zinc Plated | 10               | 7.5mm |
| 20118-877     | Steel    | 35mm   | 575mm  | Zinc Plated | 4                | 15mm  |
| 20118-894     | Steel    | 35mm   | 475mm  | Zinc Plated | 10               | 7.5mm |
| 20118-886     | Steel    | 35mm   | 275mm  | Zinc Plated | 10               | 15mm  |
| 20118-895     | Steel    | 35mm   | 575mm  | Zinc Plated | 10               | 7.5mm |
| 20118-887     | Steel    | 35mm   | 375mm  | Zinc Plated | 10               | 15mm  |
| 20118-888     | Steel    | 35mm   | 475mm  | Zinc Plated | 10               | 15mm  |
| 20118-889     | Steel    | 35mm   | 575mm  | Zinc Plated | 10               | 15mm  |

Table 2/2

| Catalog Number | Width | Quick Ship |
|----------------|-------|------------|
| 20118-878      | 125mm | No         |
| 20118-879      | 175mm | No         |
| 20118-872      | 125mm | No         |
| 20118-880      | 275mm | No         |
| 20118-890      | 125mm | No         |
| 20118-873      | 175mm | No         |
| 20118-881      | 375mm | No         |
| 20118-891      | 175mm | No         |
| 20118-882      | 475mm | No         |
| 20118-874      | 275mm | No         |
| 20118-884      | 125mm | No         |
| 20118-883      | 575mm | No         |
| 20118-892      | 275mm | No         |
| 20118-875      | 375mm | No         |
| 20118-885      | 175mm | No         |
| 20118-876      | 475mm | No         |
| 20118-893      | 375mm | No         |
| 20118-877      | 575mm | No         |

| Catalog Number | Width | Quick Ship |
|----------------|-------|------------|
| 20118-894      | 475mm | No         |
| 20118-886      | 275mm | No         |
| 20118-895      | 575mm | No         |
| 20118-887      | 375mm | No         |
| 20118-888      | 475mm | No         |
| 20118-889      | 575mm | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**