

Front Panel, Flat, With Slot for Stainless Steel EMC Gasket

Centrale d'électricité

Front panel, flat, with slot for stainless steel EMC gasket.

CERTIFICATIONS



CARACTÉRISTIQUES

Flat front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For stainless steel gasket

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish	Treated Edges
30846-682	63 HP	1	Screw-on Front			
30846-681	42 HP	1	Screw-on Front	Anodisé	Conductive	Non

Table 2/2

Référence catalogue	Hauteur	Matériau	Product Type	Rack Height	Type	Largeur
30846-682	172.9 mm	Aluminium	Panneau avant	4 U	Front Panel without Handle	319.7 mm
30846-681	172.9 mm	Aluminium	Panneau avant	4 U	Front Panel without Handle	213 mm

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE