

# MultipacPRO 19" Chassis, Steel, AlZn, Plain Top and Base

## Centrale d'électricité



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version is produced from sheet metal, Al-Zn coated and have plain top and bottom covers.

### CERTIFICATIONS



### CARACTÉRISTIQUES

Steel (AlZn coated) with Al extrusion front panel

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

EMC shielding: Approx. 20dB(A) at 2GHz without shielding material. >40dB(A) at 1Ghz with addition of stainless steel gasket between front panel and case body

Internal and external dimensions in accordance with: IEC 60297-3-101

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

### LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

| Référence catalogue | Rack Height | Profondeur | Usable Width | Montage | Conformité à                     | EMC Shielding      |
|---------------------|-------------|------------|--------------|---------|----------------------------------|--------------------|
| 20860-122           | 1 U         | 340 mm     | 447 mm       | Rack    | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-120           | 1 U         | 220 mm     | 447 mm       | Rack    | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-121           | 1 U         | 280 mm     | 447 mm       | Rack    | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-127           | 2 U         | 340 mm     | 447 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-126           | 2 U         | 280 mm     | 447 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |

Table 2/2

| Référence catalogue | Product Family | Product Type    | Type  |
|---------------------|----------------|-----------------|-------|
| 20860-122           | MultipacPRO    | Subrack/Chassis | Plein |
| 20860-120           | MultipacPRO    | Subrack/Chassis | Plein |
| 20860-121           | MultipacPRO    | Subrack/Chassis | Plein |
| 20860-127           | MultipacPRO    | Subrack/Chassis | Plein |
| 20860-126           | MultipacPRO    | Subrack/Chassis | Plein |

## ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

Telescopic slides cannot be used.

Further versions with steel front panel (pizza box) available on request.

Standardised internal mounting kits cannot be used.

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte,

une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**