

Varistar CP Double Steel Door, Perforated, 3-Point Locking

Centrale d'électricité

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

CARACTÉRISTIQUES

Double perforated steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Rack Height	Hauteur	Largeur	Couleur	Color Code	Conformité à
21630-020	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-021	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-022	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-027	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-028	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-029	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-448	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Référence catalogue	Rack Height	Hauteur	Largeur	Couleur	Color Code	Conformité à
21630-449	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-450	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-451	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-452	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-453	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-454	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-455	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Référence catalogue	Locking Type	Product Type	Protection Rating	Type	Fonctionne avec
21630-020	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-021	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-022	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-027	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-028	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-029	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-448	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-449	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-450	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

Référence catalogue	Locking Type	Product Type	Protection Rating	Type	Fonctionne avec
21630-451	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-452	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-453	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-454	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-455	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE