

Varistar CP IP 20 Cabinet, Glass Front Door, Steel Rear Door

Centrale d'électricité

Varistar : Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

CARACTÉRISTIQUES

Type of protection IP 20

With glass front door

Doors with single point locking, side panels with quick release fastener

Static load-carrying capacity 1600 kg

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/3

Référence catalogue	Rack Height	Hauteur	Frame Color	Largeur	Frame Color Code	Cladding Material
10630-038	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Acier
10630-037	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Acier
10630-039	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Acier
10630-040	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Acier

Table 2/3

Référence catalogue	Profondeur	Cladding Color	Cladding Color Code	Conformité à	Frame Material	Product Type
---------------------	------------	----------------	---------------------	--------------	----------------	--------------

10630-038	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acier	Baie
10630-037	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acier	Baie
10630-039	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acier	Baie
10630-040	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Acier	Baie

Table 3/3

Référence catalogue	Protection Rating	Charge statique
10630-038	IP20	1600 kgf
10630-037	IP20	1600 kgf
10630-039	IP20	1600 kgf
10630-040	IP20	1600 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to the doors.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE