


# Fan Control Module FCM3



Management Module for Fan Control and Voltage Monitoring.

## CERTIFICATIONS



## FONCTIONS

The fan control module (FCM3) is a standalone fan controller for 12 or 24 V fans

Up to 6 fans can be monitored and controlled

Signal monitoring of up to 6 temperature sensors

Monitoring of 3.3 V, 5 V, 12 / 24 V and -12 V voltages

FCM3 supply voltage: 12 to 24 V

Can control status LEDs for Over Temp, Fan Fail, 3.3 V, 5 V, 12 / 24 V and -12 V

In case of overheating or the failure of a fan, the other fans will be set to full speed

Status information can be queried via SMBus interface

Suitable for a 4 wire fan with PWM

## SPÉCIFICATIONS

Table 1/1

| Référence catalogue | Compatible avec     | Profondeur | Hauteur | Quantité par colis | Largeur | Expédition rapide |
|---------------------|---------------------|------------|---------|--------------------|---------|-------------------|
| 23207-170           | Systèmes CompactPCI | 119mm      | 15mm    | 1                  | 49mm    | No                |
| 23207-172           | Systèmes CompactPCI | 119mm      | 15mm    | 1                  | 40mm    | No                |

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Notre gamme complète de marques:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE