

Plaque de terre pour pied de poteau électrique



The Copper Utility Ground Plate is designed to create an equipotential plane and help protect personnel and valuable equipment. This is particularly important in the utility industry, where safety is a top priority. The plate's large surface area helps to dissipate current into the ground, reducing the risk of electrical shock and equipment damage. Additionally, the plate is available with a pigtail configuration, making it a versatile solution for various applications within the irrigation industry.

FONCTIONS

Constitue une grande surface permettant de dissiper le courant en le faisant circuler vers la terre


Envelopper autour de l'extrémité inférieure d'un poteau électrique à implanter

SPÉCIFICATIONS

Table 1/1

Référence catalogue	Connecteur	Longueur (L)	Largeur (W)	Épaisseur (T)
UGP719SBP5	Boulon fendu ESB2	489mm	191 mm	1.59 mm
UGP738SBP5	Boulon fendu ESB2	978mm	191 mm	1.59 mm
UGP738	SRGC46	978mm	191 mm	1.59 mm
UGP719	SRGC46	489mm	191 mm	1.59 mm
UGP738P5	SRGC46	978mm	191 mm	1.59 mm
UGP719BP5	SRGC46	489mm	191 mm	1.59 mm
UGP738P10	SRGC46	978mm	191 mm	1.59 mm

DIAGRAMMES



AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE