

19" Fan Unit, 1 U, Speed Control and Monitoring

Centrale d'électricité

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



CARACTÉRISTIQUES

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/1

Référence catalogue	Input Voltage AC	Input Voltage DC	Certifications
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Référence catalogue	Input Voltage AC	Input Voltage DC	Certifications
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE