

Horizontal Rail Perforated Strip

Centrale d'électricité



Perforated strip out of 1mm Aluminum for centering shielded plug-in units.

CERTIFICATIONS



CARACTÉRISTIQUES

For centering the shielded plug-in units

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Rack Width	Package Quantity	Longueur	Matériau	Product Family	Product Type
30845-189	20 HP	1	106.48 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip

Référence catalogue	Rack Width	Package Quantity	Longueur	Matériau	Product Family	Product Type
30845-209	40 HP	1	208.08 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip
34565-396	196 HP	1	1000.56 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip

Table 2/2

Référence catalogue	Fonctionne avec
30845-189	Subracks, Cases
30845-209	Subracks, Cases
34565-396	Subracks, Cases

ADDITIONAL PRODUCT DETAILS

Only usable with double-T threaded insert.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE