

nVent ERICO Ericore Underminated Conductor

Power Utilities



FONCTIONS

Low-inductance, low-impedance cable designed to minimize voltage build-up due to lightning impulses

Multiple insulated layers of conductor reduce the potential of side flashing

Requires upper and lower termination kits

SPÉCIFICATIONS

Table 1/1

Référence catalogue	Capacité	Impédance	Inductance	Résistance (Rdc)	Résistance (Rimp)	Poids unitaire
ERICORE001U	0.75 pF	12 Ω Max	37 nH	0.500 m Ω /m	6 m Ω /m	1.180 kg

INFORMATIONS PRODUIT COMPLÉMENTAIRES

Consult nVent ERICO technical support or the installation manual for guidance on maximum allowable lengths.

Inductance and Capacitance are per meter.



AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE