

QuickTerm Termination Kit



nVent PYROTENAX QuickTerm Termination Kit is a range of kits used to field-terminate #6 AWG and larger single conductor copper sheathed mineral insulated (MI) wiring cable in non-hazardous areas. It is size-for-size, allowing the MI solid conductor to be joined to an equal size flexible tail with a compression connector. The sized-up QuickTerm kit allows the MI solid conductor to be joined to a larger size flexible tail. It contains enough material to terminate two cable ends, with a special tape provided to seal the end of the MI cable.

CARACTÉRISTIQUES

Simple to install: reduces the time required to make the cable termination

Includes a special connector to splice the solid mineral insulated (MI) conductor to a flexible tail

Improved flexibility of the tail in the cabinet or enclosure

Fiabilité et longue durée de vie : 30 year product warranty available

LES CARACTÉRISTIQUES TECHNIQUES

Température maxi de service: 90 °C

Tension nominale: 600 V max

Table 1/1

Référence catalogue	Convient pour le type de câble	Taille du filetage	Type de filetage	Tail Size Required (AWG)
QT3	1/1-496	3/4"	NPT	1
QT11	1/3/0-621	1 po	NPT	3/0
QT12	1/4/0-684	1-1/4"	NPT	4/0
QT9	1/350-834	1-1/4"	NPT	350 kcmil
QT8	1/250-746	1-1/4"	NPT	250 kcmil

Référence catalogue	Convient pour le type de câble	Taille du filetage	Type de filetage	Tail Size Required (AWG)
QT10	1/500-1000	1-1/4"	NPT	500 kcmil
QT4	1/1/0-512	3/4"	NPT	1/0
QT13	1/6-340	1/2"	NPT	6
QT1	1/4-402	1/2"	NPT	4
QT14	1/2-449	3/4"	NPT	2
QT5	1/2/0-580	3/4"	NPT	2/0
QT2	1/3-449	3/4"	NPT	3

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.

Amérique du Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asie Pacifique

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Amérique latine

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT