


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

Centrale d'électricité

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



CERTIFICATIONS



CARACTÉRISTIQUES

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/3

Référence catalogue	Rack Height	Profondeur	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-474	6 U	355 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Textile
24563-473	6 U	295 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Textile
24563-472	6 U	235 mm	1	Carte fond de panier	160 mm, 220 mm	Textile
24563-174	3 U	355 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Textile
24563-173	3 U	295 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Textile
24563-172	3 U	235 mm	1	Carte fond de panier	160 mm, 220 mm	Textile

Table 2/3

Référence catalogue	Shock and Vibration Tolerance	Handle Included	Montage	Conformité à	EMC Shielding	Product Type
24563-474	5 g (force)	Non	Rack	IEC 60297-3-103	Oui	Subrack/Chassis
24563-473	5 g (force)	Non	Rack	IEC 60297-3-103	Oui	Subrack/Chassis
24563-472	5 g (force)	Non	Rack	IEC 60297-3-103	Oui	Subrack/Chassis
24563-174	5 g (force)	Non	Rack	IEC 60297-3-103	Oui	Subrack/Chassis
24563-173	5 g (force)	Non	Rack	IEC 60297-3-103	Oui	Subrack/Chassis
24563-172	5 g (force)	Non	Rack	IEC 60297-3-103	Oui	Subrack/Chassis

Table 3/3

Référence catalogue	Rack Width	Charge statique
24563-474	84 HP	15 kgf
24563-473	84 HP	15 kgf

Référence catalogue	Rack Width	Charge statique
24563-472	84 HP	15 kgf
24563-174	84 HP	15 kgf
24563-173	84 HP	15 kgf
24563-172	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE