

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

Centrale d'électricité



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

CERTIFICATIONS



CARACTÉRISTIQUES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Rack Height	Profondeur	Usable Width	Montage	Conformité à	EMC Shielding
20860-621	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-622	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-624	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-625	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-626	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-627	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-628	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-629	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-630	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-632	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-633	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-634	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-635	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Référence catalogue	Product Family	Product Type	Type	Certifications
20860-621	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-622	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-624	MultipacPRO	Subrack/Chassis	Perforé	

Référence catalogue	Product Family	Product Type	Type	Certifications
20860-625	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-626	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-627	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-628	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-629	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-630	MultipacPRO	Subrack/Chassis	Perforé	
20860-632	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-633	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-634	MultipacPRO	Subrack/Chassis	Perforé	RoHS
20860-635	MultipacPRO	Subrack/Chassis	Perforé	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE