

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Centrale d'électricité

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

CARACTÉRISTIQUES

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/3

Référence catalogue	Rack Height	Hauteur	Largeur	Couleur	Color Code	Conformité à
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Référence catalogue	Finition	Locking Type	Matériau	Product Type	Protection Rating	Type
21630-820	Revêtement laqué	3-Point Locking, Electronic	Acier	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Revêtement laqué	3-Point Locking, Electronic	Acier	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Revêtement laqué	3-Point Locking, Electronic	Acier	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Revêtement laqué	3-Point Locking, Electronic	Acier	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Revêtement laqué	3-Point Locking, Electronic	Acier	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Revêtement laqué	3-Point Locking, Electronic	Acier	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Référence catalogue	Fonctionne avec
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE