

Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking

Centrale d'électricité

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

CARACTÉRISTIQUES

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2						
Référence catalogue	Rack Height	Hauteur	Largeur	Couleur	Color Code	Conformité à
21630-876	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-877	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-878	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-879	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-880	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-881	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-882	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Référence catalogue	Rack Height	Hauteur	Largeur	Couleur	Color Code	Conformité à
21630-883	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Table 2/2

Référence catalogue	Locking Type	Matériau	Product Type	Protection Rating	Type	Fonctionne avec
21630-876	4-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-877	4-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-878	4-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-879	4-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-880	4-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-881	4-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-882	5-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-883	5-Point Locking	Acier	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE