

# EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

## Centrale d'électricité

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



### CERTIFICATIONS



### CARACTÉRISTIQUES

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

## LES CARACTÉRISTIQUES TECHNIQUES

Table 1/3

| Référence catalogue | Rack Height | Profondeur | Package Quantity | For Mounting         | Board Depth                    | EMC Gasket Type  |
|---------------------|-------------|------------|------------------|----------------------|--------------------------------|------------------|
| 24567-161           | 3 U         | 175 mm     | 1                | Carte fond de panier | 160 mm                         | Acier inoxydable |
| 24567-162           | 3 U         | 235 mm     | 1                | Carte fond de panier | 160 mm, 220 mm                 | Acier inoxydable |
| 24567-163           | 3 U         | 295 mm     | 1                | Carte fond de panier | 160 mm, 220 mm, 280 mm         | Acier inoxydable |
| 24567-164           | 3 U         | 355 mm     | 1                | Carte fond de panier | 160 mm, 220 mm, 280 mm, 340 mm | Acier inoxydable |
| 24567-461           | 6 U         | 175 mm     | 1                | Carte fond de panier | 160 mm                         | Acier inoxydable |
| 24567-462           | 6 U         | 235 mm     | 1                | Carte fond de panier | 160 mm, 220 mm                 | Acier inoxydable |
| 24567-463           | 6 U         | 295 mm     | 1                | Carte fond de panier | 160 mm, 220 mm, 280 mm         | Acier inoxydable |
| 24567-464           | 6 U         | 355 mm     | 1                | Carte fond de panier | 160 mm, 220 mm, 280 mm, 340 mm | Acier inoxydable |

Table 2/3

| Référence catalogue | Shock and Vibration Tolerance | Handle Included | Montage | Conformité à    | EMC Shielding | Product Type    |
|---------------------|-------------------------------|-----------------|---------|-----------------|---------------|-----------------|
| 24567-161           | 5 g (force)                   | Oui             | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |
| 24567-162           | 5 g (force)                   | Oui             | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |
| 24567-163           | 5 g (force)                   | Oui             | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |
| 24567-164           | 5 g (force)                   | Oui             | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |
| 24567-461           | 5 g (force)                   | Oui             | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |
| 24567-462           | 5 g (force)                   | Oui             | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |

| Référence catalogue | Shock and Vibration Tolerance | HandleIncluded | Montage | Conformité à    | EMC Shielding | Product Type    |
|---------------------|-------------------------------|----------------|---------|-----------------|---------------|-----------------|
| 24567-463           | 5 g (force)                   | Oui            | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |
| 24567-464           | 5 g (force)                   | Oui            | Rack    | IEC 60297-3-103 | Non           | Subrack/Chassis |

Table 3/3

| Référence catalogue | Rack Width | Charge statique | Certifications |
|---------------------|------------|-----------------|----------------|
| 24567-161           | 84 HP      | 15 kgf          | RoHS           |
| 24567-162           | 84 HP      | 15 kgf          | RoHS, DB       |
| 24567-163           | 84 HP      | 15 kgf          | RoHS, DB       |
| 24567-164           | 84 HP      | 15 kgf          | RoHS, DB       |
| 24567-461           | 84 HP      | 15 kgf          | RoHS, DB       |
| 24567-462           | 84 HP      | 15 kgf          | RoHS, DB       |
| 24567-463           | 84 HP      | 15 kgf          | RoHS, DB       |
| 24567-464           | 84 HP      | 15 kgf          | RoHS, DB       |

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : [www.nvent.com](http://www.nvent.com) et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**