

Fan Unit With Housing for 19" Pusher Fan, 2 U, Axial

Centrale d'électricité

Supplementary fan (built-on) with housing for Schroff pusher fan 2 U. No additional voltage supply necessary: connection is via 19" pusher fan.

CERTIFICATIONS



CARACTÉRISTIQUES

Extra 2 U useable space: by using a built-on fan, components mounted below the 19" pusher fan can be cooled

No additional voltage supply necessary: connection is via 19" pusher fan, 2 U

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/1

Référence catalogue	Type	Couleur	Input Voltage AC
10713-530	Système de ventilation	Silver	230 V min

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE