

19" Fan Unit, 1 U, Speed Control and Monitoring

Power Utilities

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



FONCTIONS

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPÉCIFICATIONS

Table 1/1

Référence catalogue	Tension d'entrée CA	Tension d'entrée CC	Certifications
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Référence catalogue	Tension d'entrée CA	Tension d'entrée CC	Certifications
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE