

19" Pusher Fan, 2 U, Axial

Power Utilities

Fan tray with integrated pusher fan.



CERTIFICATIONS



FONCTIONS

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

SPÉCIFICATIONS

Table 1/1

Référence catalogue	Tension d'entrée CA	Tension d'entrée CC
10713-534	230 V min	
10713-518	230 V min	

Référence catalogue	Tension d'entrée CA	Tension d'entrée CC
10713-526	230 V min	
10713-536	115 V min	
10713-520	115 V min	
10713-537		24 V min
10713-529		24 V min
19713-540		

INFORMATIONS PRODUIT COMPLÉMENTAIRES

Please order mains cable separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE