

Matériau de soudure nVent ERICO Cadweld Plus F20



nVent ERICO Cadweld Plus Welding Material, F20, allows for an expedited, permanent grounding connection using pre-measured, self-contained cups. Each package of welding material can be easily placed into the mold and safely ignited with the nVent ERICO Cadweld Plus Impulse Exothermic Welding Control Unit to create an irreversible bond.

CERTIFICATIONS



FONCTIONS

Le mélange est composé principalement d'oxyde de cuivre et d'aluminium

Utilisé principalement dans les applications de mise à la terre et de métallisation

Kit de matériaux de soudage intégré

Code en couleurs par taille pour faciliter l'identification

Allumage électronique

Aucune poudre d'allumage requise

Non explosif

N'est pas sujet à un allumage spontané

Voir les détails spécifiques de l'assemblage nVent ERICO Cadweld pour déterminer les exigences liées aux matériaux de soudage

SPÉCIFICATIONS

Table 1/1

Référence catalogue	Référence article	Anneau de teinte RAL	Conformité	Certifications
---------------------	-------------------	----------------------	------------	----------------

15PLUSF20	165700	Noir		UL, cUL
400PLUSF20	165711	Marron		
150PLUSF20	165707	Bleu foncé	Connexion permanente EN CEI® 62561-1	UL, cUL
65PLUSF20	165704	Vert foncé	Connexion permanente EN CEI® 62561-1	cUL, UL
32PLUSF20	165702	Blanc	Connexion permanente EN CEI® 62561-1	cUL, UL
90PLUSF20	165705	Gris	Connexion permanente EN CEI® 62561-1	cUL, UL
45PLUSF20	165703	Bleu clair	Connexion permanente EN CEI® 62561-1	cUL, UL
25PLUSF20	165701	Rouge	Connexion permanente EN CEI® 62561-1	cUL, UL
115PLUSF20	165706	Orange	Connexion permanente EN CEI® 62561-1	UL, cUL
500PLUSF20	165712	Marron clair		
300PLUSF20	165710	Vert clair		UL, cUL
250PLUSF20	165709	Violet		UL, cUL
600PLUSF20		Blanc		
750PLUSF20	164996	Blanc		
200PLUSF20	165708	Jaune		UL, cUL

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

⚠ WARNING: This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Notre gamme complète de marques:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE