


Kit de mise à la masse Propac PRO

RÉFÉRENCE CATALOGUE

21102-001



Mise à la terre selon : DIN EN 50178, VDE 0160 DIN EN 62368-1, VDE 0805 DIN EN 61010-1, VDE 0411 Partie 1 DIN EN 61010-1A2, VDE 0411 Partie 1/A1.

CERTIFICATIONS



FONCTIONS

Mise à la masse conforme : DIN EN 50178/VDE 0160 DIN EN 62368-1/VDE 0805 DIN EN 61010-1 /VDE 0411 partie 1 DIN EN 61010-1A2 /VDE 0411 partie 1/A1

Testé VDE

DIN EN 50178/VDE 0160DIN EN 62368-1/VDE 0805 DIN EN 61010-1/VDE 0411 partie 1DIN EN 61010-1A2/VDE 0411 partie 1/A1

ATTRIBUTS DU PRODUIT

Type de produit: Kit de mise à la masse

Famille de produits: PropacPRO

Type: Kit de mise à la masse

Compatible avec: Coffrets

Quantité par colis: 1

Net Weight: 0.03kg

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Notre gamme complète de marques:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE