

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Centrale d'électricité

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICATIONS



CARACTÉRISTIQUES

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/3

Référence catalogue	Rack Height	Profondeur	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24567-161	3 U	175 mm	1	Carte fond de panier	160 mm	Acier inoxydable
24567-162	3 U	235 mm	1	Carte fond de panier	160 mm, 220 mm	Acier inoxydable
24567-163	3 U	295 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Acier inoxydable
24567-164	3 U	355 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm, 340 mm	Acier inoxydable
24567-461	6 U	175 mm	1	Carte fond de panier	160 mm	Acier inoxydable
24567-462	6 U	235 mm	1	Carte fond de panier	160 mm, 220 mm	Acier inoxydable
24567-463	6 U	295 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm	Acier inoxydable
24567-464	6 U	355 mm	1	Carte fond de panier	160 mm, 220 mm, 280 mm, 340 mm	Acier inoxydable

Table 2/3

Référence catalogue	Shock and Vibration Tolerance	Handle Included	Montage	Conformité à	EMC Shielding	Product Type
24567-161	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis
24567-162	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis
24567-163	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis
24567-164	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis
24567-461	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis
24567-462	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis

Référence catalogue	Shock and Vibration Tolerance	HandleIncluded	Montage	Conformité à	EMC Shielding	Product Type
24567-463	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis
24567-464	5 g (force)	Oui	Rack	IEC 60297-3-103	Non	Subrack/Chassis

Table 3/3

Référence catalogue	Rack Width	Charge statique	Certifications
24567-161	84 HP	15 kgf	RoHS
24567-162	84 HP	15 kgf	RoHS, DB
24567-163	84 HP	15 kgf	RoHS, DB
24567-164	84 HP	15 kgf	RoHS, DB
24567-461	84 HP	15 kgf	RoHS, DB
24567-462	84 HP	15 kgf	RoHS, DB
24567-463	84 HP	15 kgf	RoHS, DB
24567-464	84 HP	15 kgf	RoHS, DB

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE