

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Centrale d'électricité

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



CERTIFICATIONS



CARACTÉRISTIQUES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/3

Référence catalogue	Rack Height	Profondeur	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-191	3 U	175 mm	1	DIN Connector	160 mm	Acier inoxydable
24563-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Acier inoxydable
24563-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Acier inoxydable
24563-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Acier inoxydable
24563-491	6 U	175 mm	1	DIN Connector	160 mm	Acier inoxydable
24563-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Acier inoxydable
24563-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Acier inoxydable
24563-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Acier inoxydable

Table 2/3

Référence catalogue	Handle Included	Montage	Conformité à	EMC Shielding	Product Type	Rack Width
24563-191	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP
24563-192	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP
24563-193	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP
24563-194	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP
24563-491	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP
24563-492	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP
24563-493	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP

Référence catalogue	HandleIncluded	Montage	Conformité à	EMC Shielding	Product Type	Rack Width
24563-494	Non	Rack	IEC 60297-3-103	Non	Subrack/Chassis	84 HP

Table 3/3

Référence catalogue	Charge statique
24563-191	11 kgf
24563-192	11 kgf
24563-193	11 kgf
24563-194	11 kgf
24563-491	11 kgf
24563-492	11 kgf
24563-493	11 kgf
24563-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE