

RackPower Basic PDU, RB0xxx, 100-240 VAC, 1-phase

Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

FONCTIONS

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPÉCIFICATIONS

Table 1/2

Référence catalogue	Type de produit	Type de prise	Couleur	Longueur	Tension CA	Profondeur
RB0322	Bâti de prises	CEI C13, CEI C19	Noir	817 mm	230 V	53 mm

Table 2/2

Référence catalogue	Largeur
RB0322	52 mm

INFORMATIONS PRODUIT COMPLÉMENTAIRES

Please order bracket for vertical mounting separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.



Notre gamme complète de marques:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE