

Varistar CP Swing Frame for 800 mm Width

Centrale d'électricité

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

CARACTÉRISTIQUES

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

LES CARACTÉRISTIQUES TECHNIQUES

Table 1/2

Référence catalogue	Rack Height	Couleur	Color Code	Hauteur	Matériau	Product Type
21630-669	24 U	Black Grey	RAL 7021	1200 mm	Acier	Cabinet/Rack Frame
21630-680	24 U	Black Grey	RAL 7021	1200 mm	Acier	Cabinet/Rack Frame
21630-671	29 U	Black Grey	RAL 7021	1400 mm	Acier	Cabinet/Rack Frame
21630-681	29 U	Black Grey	RAL 7021	1400 mm	Acier	Cabinet/Rack Frame
21630-673	33 U	Black Grey	RAL 7021	1600 mm	Acier	Cabinet/Rack Frame
21630-682	33 U	Black Grey	RAL 7021	1600 mm	Acier	Cabinet/Rack Frame
21630-675	38 U	Black Grey	RAL 7021	1800 mm	Acier	Cabinet/Rack Frame

Référence catalogue	Rack Height	Couleur	Color Code	Hauteur	Matériau	Product Type
21630-683	38 U	Black Grey	RAL 7021	1800 mm	Acier	Cabinet/Rack Frame
21630-677	42 U	Black Grey	RAL 7021	2000 mm	Acier	Cabinet/Rack Frame
21630-684	42 U	Black Grey	RAL 7021	2000 mm	Acier	Cabinet/Rack Frame
21630-679	47 U	Black Grey	RAL 7021	2200 mm	Acier	Cabinet/Rack Frame
21630-685	47 U	Black Grey	RAL 7021	2200 mm	Acier	Cabinet/Rack Frame

Table 2/2

Référence catalogue	Protection Rating	Largeur
21630-669	IP20	800 mm
21630-680	IP20	800 mm
21630-671	IP20	800 mm
21630-681	IP20	800 mm
21630-673	IP20	800 mm
21630-682	IP20	800 mm
21630-675	IP20	800 mm
21630-683	IP20	800 mm
21630-677	IP20	800 mm
21630-684	IP20	800 mm
21630-679	IP20	800 mm
21630-685	IP20	800 mm

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés conformément aux consignes figurant dans les fiches d'instructions et les documents de formation des produits nVent. Les fiches d'instructions sont disponibles à l'adresse suivante : www.nvent.com et auprès de votre représentant du service client nVent. Une mauvaise installation, une utilisation incorrecte, une application erronée ou toute autre forme de non-respect scrupuleux des instructions et avertissements de nVent peuvent entraîner un dysfonctionnement du produit, des dommages matériels, des lésions corporelles graves et le décès et/ou annuler votre garantie.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE