


Poignée d'insertion/extraction, type IET, levier gris, bouton-poussoir noir, bas, 10 pièces

RÉFÉRENCE CATALOGUE

20817-660



Poignée d'insertion/d'extraction, de type IET, conforme à l'IEEE 1101.10. Décalage 0,1". Pour une force d'insertion/extraction jusqu'à 700 N (par paire).

CERTIFICATIONS



FONCTIONS

Pour des forces d'insertion et d'extraction jusqu'à 700 N (par paire)

Conforme à la norme IEEE 1101.10 et IEC 60297-3-102

Possibilité de monter un microswitch

Avec verrouillage

Codifiable conformément à IEEE 1101.10 et IEC 60297-3-103

Quantité par colis: 10

Indice d'inflammabilité: UL® 94V-0

Couleur: Gris

Conformité: EN 45545-2

Type de produit: Poignée

Compatible avec: Faces avant

Veuillez commander séparément les pions de détrompage et le microswitch

Technical drawing of a door handle assembly. The drawing includes an exploded view of the handle and a detailed view of the handle body with dimensions. The exploded view shows the handle (4.07) and the mounting plate (2.54) with dimensions 20, 2.54, 2.54, 7.62, and 1.07. The detailed view of the handle body shows dimensions 2.5, 6.1, 14, 3.6, 2.5, 3.8, 4.5, 8.15, 6.95, 2.95, 26, 12.75, 22.75, and 2.5. The label 'bottom' is present.

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Notre gamme complète de marques:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE