

# Guarnizioni foro per aree pericolose

Hazardous Location Hole Seals are designed to be used on Increased Safety (Ex e) enclosures in ATEX or IECEx Zone 1 or 2 hazardous areas. Certified to be used on metallic, non-painted enclosures, these hole seals ensure a dust-, oil- and water-tight seal. Designed to seal extra pushbutton holes, conduit openings and knockout openings, these self-centering hole seals are easy to install.

## STANDARD INDUSTRIALI

UL 508A Component Recognized; Type 4, 4X, 12, 3R; File No. E61997

cUR Component Recognized per CSA C22.2 No. 94; Type 4, 4X, 12, 3R; File No. 42186

IECEx and ATEX Approvals

Suitable for use on increased safety enclosures for ZONE 1 or ZONE

2 assemblies

ATEX Directive 94/9/EC

ATEX

Ex e IIC Gb

Ex tb IIIC Db IP 66

Sira 14ATEX3233U

IECEx

Ex e IIC Gb

Ex tb IIIC Db IP 66

IECEx SIR 14.0073U

NEMA/EEMAC Type 3R, 4, 4X, 12

IEC 60529, IP66



## CARATTERISTICHE

Secure sealing with silicon rubber gasket to protect against water and dust ingress in extreme temperature applications ranging from -55 C (-67 F) to 180 C (356 F)

Seal pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water

Easy installation in enclosure cutouts with self-centering hole seals

Hole seals are available in metric and english standard hole sizes

SPECIFICHE

Fine: Spazzolato  
Materiale: Acciaio inox 316L

| Table 1/1         |                   |                       |                        |                   |
|-------------------|-------------------|-----------------------|------------------------|-------------------|
| Codice a catalogo | Diametro del foro | Diametro dell'assieme | Dimensione filettatura | Spedizione rapida |
| EXAS250SS6        | 75mm              | 93mm                  | M75                    | No                |
| EXAS100SS6        | 32mm              | 48mm                  | M32                    | No                |
| EXAS150SS6        | 50mm              | 67mm                  | M50                    | No                |
| EXAS075SS6        | 25mm              | 43mm                  | M25                    | No                |
| EXAS050SS6        | 20mm              | 35mm                  | M20                    | No                |
| EXAS125SS6        | 40mm              | 59mm                  | M40                    | No                |
| EXAS200SS6        | 63mm              | 80mm                  | M63                    | No                |

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE