

Additivo per arachidi HYA15HT Interlok nVent, temperatura calda



The nVent LENTON HYA15LM Grout Additive, Hot Temperature is designed to be used in conjunction with nVent LENTON Interlok grout-fill couplers and nVent LENTON Interlok HY15LM Grout. The additive is used to increase working time of the grout during hot temperature applications which allows for a longer time window to place the grout into the Interlok couplers. This proprietary grout additive increases the maximum working temperature of HY15LM grout from 100 °F (38 °C) to 122 °F (50 °C).

CARATTERISTICHE

Allows for hot temperature grouting

Increases grout working time in hot climates

Extends the construction season

For use in pump or gravity fill applications

SPECIFICHE

Table 1/1

Codice a catalogo	Resistenza alla compressione	Temperatura di esercizio	Peso unità
HYA15HT	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	21 to 50 °C	0.05 kg

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

For use with HY15LM grout only.

Hot weather concreting procedures, such as ACI 305 Hot Weather Concreting, must be followed.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

HYA15HT can be used in temperatures as low as 70 °F (21 °C) to extend working time; however, this may slow the compressive strength curve.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221

Opzione 1 – Assistenza
clienti

Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Germania:

800 1890272

altri paesi:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE