

T-Series Vertical Splice Kit



T-Series splice kits contain the following: Sleeve, filler material kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), pouring basin and pouring basin crucible. Splice kits are ordered based on the quantity of splices needed. Sleeves and filler material kits are one-time use parts. Pouring basins and crucibles are prorated based on their anticipated life. Ordering splice kits simplifies ordering, reduces order errors and helps ensure proper sizing of components. Kits can be ordered with longer (extended) sleeves for use when the reinforcing steel deformation pattern or spacing does not meet the minimum product specifications.

CARATTERISTICHE

Simplifies ordering

Used to splice the same diameter bars

Available with extended sleeve lengths

SPECIFICHE

Table 1/2

Codice a catalogo	Manicotto	Dimensioni tondino spiralato, unità metriche	Dimensioni tondino spiralato, USA	Dimensioni tondino spiralato, Canada	Lunghezza 1 (L1)	Lunghezza 2 (L2)
RBT1091	Lunghezza standard	32 mm	#10		362 mm	51 mm
RBT10911	Lunghezza estesa	32 mm	#10		362 mm	51 mm
RBT4101	Lunghezza standard	12 mm	#4	10M	349 mm	51 mm
RBT5101	Lunghezza standard	16 mm	#5	15M	349 mm	51 mm
RBT6101	Lunghezza standard	20 mm	#6	20M	349 mm	51 mm
RBT7101	Lunghezza standard	22 mm	#7		356 mm	51 mm

Codice a catalogo	Manicotto	Dimensioni tondino spiralato, unità metriche	Dimensioni tondino spiralato, USA	Dimensioni tondino spiralato, Canada	Lunghezza 1 (L1)	Lunghezza 2 (L2)
RBT8101	Lunghezza standard	25 mm	#8	25M	356 mm	51 mm
RBT9101	Lunghezza standard	28 mm	#9	30M	362 mm	51 mm
RBT91011	Lunghezza estesa	28 mm	#9	30M	362 mm	51 mm
RBT91012	Lunghezza estesa	28 mm	#9	30M	362 mm	51 mm
RBT11101	Lunghezza standard	36 mm	#11	35M	375 mm	64 mm
RBT111011	Lunghezza estesa	36 mm	#11	35M	375 mm	64 mm
RBT14101	Lunghezza standard	43 mm	#14	45M	387 mm	64 mm
RBT1891	Lunghezza standard	57 mm	#18	55M	406 mm	64 mm

Table 2/2

Codice a catalogo	Altezza 1 (H1)	Altezza 2 (H2)	Altezza 3 (H3)	Altezza 4 (H4)	Diametro (Ø)
RBT1091	660mm	451mm	210mm	197mm	127 mm
RBT10911	660mm	451mm	222mm	210mm	127 mm
RBT4101	641mm	451mm	191mm	197mm	102 mm
RBT5101	641mm	451mm	191mm	197mm	102 mm
RBT6101	654mm	451mm	203mm	197mm	102 mm
RBT7101	654mm	451mm	203mm	197mm	102 mm
RBT8101	654mm	451mm	203mm	197mm	102 mm
RBT9101	654mm	451mm	203mm	197mm	102 mm

Codice a catalogo	Altezza 1 (H1)	Altezza 2 (H2)	Altezza 3 (H3)	Altezza 4 (H4)	Diametro (Ø)
RBT91011	654mm	451mm	216mm	210mm	127 mm
RBT91012	654mm	451mm	229mm	222mm	127 mm
RBT11101	686mm	216mm	216mm	210mm	127 mm
RBT111011	686mm	216mm	229mm	222mm	152 mm
RBT14101	775mm	546mm	229mm	222mm	152 mm
RBT1891	838mm	584mm	254mm	216mm	178 mm

INFORMAZIONI DI PRODOTTO AGGIUNTIVE


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

All dimensions are for reference only.

Components can also be purchased separately: (1) Sleeve, (2) Filler Material Kit (filler material, packing, pouring basin ceramic insert and disk, pouring basin ceramic guide tube), (3) Pouring Basin, and (4) Pouring Basin Crucible.

Splice Kit Components							
Splice Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube	Sleeve	Pouring Basin	Pouring Basin Crucible
RBT4101	RBF40	RBS354710 RBS35475	RBS5037	RBS5038	RBT5101A	RBWS1500U	RBWS22774
RBT5101	RBF40	RBS354710 RBS35475	RBS5037	RBS5038	RBT5101A	RBWS1500U	RBWS22774
RBT6101	RBF50	RBS35473.5 RBS35477	RBS5037	RBS5038	RBT6101A	RBWS1500X	RBWS22774
RBT7101	RBF50	RBS35474 RBS35478	RBS5037	RBS5038	RBT7101A	RBWS1500A	RBWS22774
RBT8101	RBF55	RBS354710 RBS35475	RBS5037	RBS5038	RBT8101A	RBWS1500C	RBWS22774
RBT9101	RBF80	RBS354711 RBS35475.5	RBS5037	RBS5038	RBT9101A	RBWS1500D	RBWS22774
RBT91011	RBF90	RBS354711 RBS35475.5	RBS5037	RBS5038	RBT91011A	RBWS1499D	RBWS22775
RBT91012	RBF105	RBS354711 RBS35475.5	RBS5037	RBS5038	RBT91012A	RBWS1500D	RBWS22775
RBT1091	RBF90	RBS354712 RBS35476	RBS5037	RBS5038	RBT1091A	RBWS1500E	RBWS22775
RBT10911	RBF105	RBS354712 RBS35476	RBS5037	RBS5038	RBT10911A	RBWS1500E	RBWS22775
RBT11101	RBF105	RBS354712 RBS35476	RBS5037	RBS5038	RBT11101A	RBWS1499F	RBWS22775
RBT111011	RBF125	RBS354712 RBS35476	RBS5037	RBS5038	RBT111011A	RBWS1481F	RBWS22776
RBT14101	RBF195	RBS354715 RBS35477	RBS5037	RBS5039	RBT14101A	RBWS1481J	RBWS22776
RBT1891	RBF270	RBS354720 RBS35479	RBS5037	RBS5039	RBT1891A	RBWS1482M	RBWS22777

SCHEMI



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni

personali e morte e/o annullare la vostra garanzia.

Nord America

+1.800.753.9221
Opzione 1 – Assistenza
clienti
Opzione 2 – Assistenza
tecnica

Europa

Paesi Bassi:
+31 800-0200135
Francia:
+33 800 901 793

Europa

Germania:
800 1890272
altri paesi:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE