


19" Pusher Fan, 3 U, Axial

Servizi di distribuzione di energia

Fan tray with integrated pusher fan.



CERTIFICAZIONI



CARATTERISTICHE

Ventilation directed accurately to the electronics

19" Pusher Fan, 3 U, Axial

Air infeed from front, air exits at the top rear of cabinet (guided upwards by cover plates or via hoses to rear and upwards)

Contact protection in accordance with DIN EN ISO 13857

SPECIFICHE

Table 1/1

Numero catalogo	Input Voltage AC
10713-546	230 V min
10713-547	115 V min

ADDITIONAL PRODUCT DETAILS

With cover plates, this pusher fan can be re-fitted to different cooling concepts

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE