

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Servizi di distribuzione di energia

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICAZIONI



CARATTERISTICHE

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Profondità	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24567-161	3 U	175 mm	1	Backplane	160 mm	Acciaio inossidabile
24567-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Acciaio inossidabile
24567-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Acciaio inossidabile
24567-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acciaio inossidabile
24567-461	6 U	175 mm	1	Backplane	160 mm	Acciaio inossidabile
24567-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Acciaio inossidabile
24567-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Acciaio inossidabile
24567-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Acciaio inossidabile

Table 2/3

Numero catalogo	Shock and Vibration Tolerance	Handle Included	Montaggio	È conforme a	EMC Shielding	Product Type
24567-161	5 g (force)	Sì.	Rack	IEC 60297-3-103	No	Subrack/Chassis
24567-162	5 g (force)	Sì.	Rack	IEC 60297-3-103	No	Subrack/Chassis
24567-163	5 g (force)	Sì.	Rack	IEC 60297-3-103	No	Subrack/Chassis
24567-164	5 g (force)	Sì.	Rack	IEC 60297-3-103	No	Subrack/Chassis
24567-461	5 g (force)	Sì.	Rack	IEC 60297-3-103	No	Subrack/Chassis
24567-462	5 g (force)	Sì.	Rack	IEC 60297-3-103	No	Subrack/Chassis

Numero catalogo	Shock and Vibration Tolerance	HandleIncluded	Montaggio	È conforme a	EMC Shielding	Product Type
24567-463	5 g (force)	Si.	Rack	IEC 60297-3-103	No	Subrack/Chassis
24567-464	5 g (force)	Si.	Rack	IEC 60297-3-103	No	Subrack/Chassis

Table 3/3			
Numero catalogo	Rack Width	Carico statico	Certificazioni
24567-161	84 HP	15 kgf	RoHS
24567-162	84 HP	15 kgf	RoHS, DB
24567-163	84 HP	15 kgf	RoHS, DB
24567-164	84 HP	15 kgf	RoHS, DB
24567-461	84 HP	15 kgf	RoHS, DB
24567-462	84 HP	15 kgf	RoHS, DB
24567-463	84 HP	15 kgf	RoHS, DB
24567-464	84 HP	15 kgf	RoHS, DB

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE