


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

Servizi di distribuzione di energia

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



CERTIFICAZIONI



CARATTERISTICHE

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Profondità	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-172	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-173	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-174	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-472	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-473	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-474	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/3

Numero catalogo	Shock and Vibration Tolerance	Handle Included	Montaggio	È conforme a	EMC Shielding	Product Type
24563-172	5 g (force)	No	Rack	IEC 60297-3-103	Sì.	Subrack/Chassis
24563-173	5 g (force)	No	Rack	IEC 60297-3-103	Sì.	Subrack/Chassis
24563-174	5 g (force)	No	Rack	IEC 60297-3-103	Sì.	Subrack/Chassis
24563-472	5 g (force)	No	Rack	IEC 60297-3-103	Sì.	Subrack/Chassis
24563-473	5 g (force)	No	Rack	IEC 60297-3-103	Sì.	Subrack/Chassis
24563-474	5 g (force)	No	Rack	IEC 60297-3-103	Sì.	Subrack/Chassis

Table 3/3

Numero catalogo	Rack Width	Carico statico
24563-172	84 HP	15 kgf
24563-173	84 HP	15 kgf

Numero catalogo	Rack Width	Carico statico
24563-174	84 HP	15 kgf
24563-472	84 HP	15 kgf
24563-473	84 HP	15 kgf
24563-474	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE