

EuropacPRO 19" Subrack Kit for Backplane, Rugged, Shielded

Servizi di distribuzione di energia

Subrack with reinforced horizontal rails and side panels for backplane mounting.



CERTIFICAZIONI



CARATTERISTICHE

Subrack with side panel and horizontal rail, type R "rugged" with 3 hole fixing for increased stability (+60% compared to 2 hole fixing of "Heavy" rails)

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip. Special adaptor rails allow conduction cooled assemblies to be fitted

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, - 102, -103, IEEE 1101.1, IEEE 1101.10

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Shock and vibration tested to MIL 167, IEC 61587 DL 3, MIL 810 G, MIL 901D. Shock and vibration resistant in all three axial directions.

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available. Subrack with telescoping slides can be adopted for cabinet mounting on request

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Profondità	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24567-149	3 U	295 mm	1	Backplane	160 mm	Textile
24567-449	6 U	295 mm	1	Backplane	160 mm	Textile

Table 2/3

Numero catalogo	Shock and Vibration Tolerance	Handle Included	Montaggio	È conforme a	EMC Shielding	Product Type
24567-149	25 g (force)	Sì.	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	Sì.	Subrack/Chassis
24567-449	25 g (force)	Sì.	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	Sì.	Subrack/Chassis

Table 3/3

Numero catalogo	Rack Width	Carico statico
24567-149	84 HP	25 kgf
24567-449	84 HP	25 kgf

ADDITIONAL PRODUCT DETAILS

Test reports online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE