

Front Panel, Anodized, Unshielded, Screw Assembly

Servizi di distribuzione di energia

Anodized front panel, unshielded version, Al, 2.5 mm.



CERTIFICAZIONI



CARATTERISTICHE

Partial width front panel, Al, 2.5 mm

Al, anodized

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Rack Width	Package Quantity	Montaggio	Front Finish	Rear Finish
30807-416	2 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-494	3 U	42 HP	1	Screw-on Front	Anodized	Anodized

Numero catalogo	Rack Height	Rack Width	Package Quantity	Montaggio	Front Finish	Rear Finish
30807-506	3 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-596	4 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-764	6 U	42 HP	1	Screw-on Front	Anodized	Anodized
30807-771	6 U	63 HP	1	Screw-on Front	Anodized	Anodized
30807-776	6 U	84 HP	1	Screw-on Front	Anodized	Anodized
30808-067	3 U	63 HP	1	Screw-on Front	Anodized	Anodized
30810-432	3 U	2 HP	5	Screw-on Front	Anodized	Anodized
30818-741	6 U	2 HP	5	Screw-on Front	Anodized	Conductive
30807-481	3 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-482	3 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-483	3 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-484	3 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-485	3 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-487	3 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-496	3 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-501	3 U	14 HP	5	Screw-on Front	Anodized	Anodized
30807-508	3 U	3 HP	5	Screw-on Front	Anodized	Anodized
30807-509	3 U	7 HP	5	Screw-on Front	Anodized	Anodized

Numero catalogo	Rack Height	Rack Width	Package Quantity	Montaggio	Front Finish	Rear Finish
30807-510	3 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-778	6 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-777	6 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-752	6 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-753	6 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-755	6 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-757	6 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-758	6 U	14 HP	5	Screw-on Front	Anodized	Conductive
30807-766	6 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-779	6 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-780	6 U	16 HP	5	Screw-on Front	Anodized	Anodized
30807-833	6 U	7 HP		Screw-on Front	Anodized	Anodized

Table 2/3

Numero catalogo	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale	Product Type
30807-416	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Alluminio	Front Panel
30807-494	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-506	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel

Numero catalogo	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale	Product Type
30807-596	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	172.9 mm	Alluminio	Front Panel
30807-764	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-771	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-776	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30808-067	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30810-432	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30818-741	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-481	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-482	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-483	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-484	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-485	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-487	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-496	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel

Numero catalogo	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale	Product Type
30807-501	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-508	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-509	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-510	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio	Front Panel
30807-778	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-777	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-752	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-753	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-755	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-757	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-758	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-766	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-779	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel
30807-780	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel

Numero catalogo	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale	Product Type
30807-833	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio	Front Panel

Table 3/3

Numero catalogo	Tipo	Larghezza	Certificazioni
30807-416	Front Panel without Handle	426.4 mm	RoHS
30807-494	Front Panel without Handle	213 mm	RoHS
30807-506	Front Panel without Handle	426.4 mm	RoHS
30807-596	Front Panel without Handle	426.4 mm	
30807-764	Front Panel without Handle	213 mm	RoHS
30807-771	Front Panel without Handle	319.7 mm	RoHS
30807-776	Front Panel without Handle	426.4 mm	RoHS
30808-067	Front Panel without Handle	319.7 mm	RoHS
30810-432	Front Panel without Handle	9.8 mm	RoHS
30818-741	Front Panel without Handle	9.8 mm	RoHS
30807-481	Front Panel without Handle	20 mm	RoHS
30807-482	Front Panel without Handle	30.1 mm	RoHS
30807-483	Front Panel without Handle	50.5 mm	RoHS
30807-484	Front Panel without Handle	40.3 mm	RoHS
30807-485	Front Panel without Handle	60.6 mm	RoHS

Numero catalogo	Tipo	Larghezza	Certificazioni
30807-487	Front Panel without Handle	106.3 mm	RoHS
30807-496	Front Panel without Handle	141.9 mm	RoHS
30807-501	Front Panel without Handle	70.8 mm	RoHS
30807-508	Front Panel without Handle	14.9 mm	RoHS
30807-509	Front Panel without Handle	35.2 mm	RoHS
30807-510	Front Panel without Handle	25 mm	RoHS
30807-778	Front Panel without Handle	20 mm	RoHS
30807-777	Front Panel without Handle	25 mm	RoHS
30807-752	Front Panel without Handle	30.1 mm	RoHS
30807-753	Front Panel without Handle	50.5 mm	RoHS
30807-755	Front Panel without Handle	60.6 mm	RoHS
30807-757	Front Panel without Handle	106.3 mm	RoHS
30807-758	Front Panel without Handle	70.8 mm	RoHS
30807-766	Front Panel without Handle	141.9 mm	RoHS
30807-779	Front Panel without Handle	40.3 mm	RoHS
30807-780	Front Panel without Handle	80.9 mm	RoHS
30807-833	Front Panel without Handle	35.2 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE