

Guide Rail Multi Piece, Mid-Piece Aluminium/Plastic Extrusion

Servizi di distribuzione di energia

CARATTERISTICHE

Middle profile for mounting guide rails for 2.5 mm groove width

2 plastic end pieces are required; these are pushed on to both ends of the middle profile

Guide rails can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Storage temperature: from -40 °C ... 130 °C

SPECIFICHE

Table 1/1

Numero catalogo	Board Depth	Colore	Groove Width	Materiale	Tipo	Works With
34562-813	160 mm	Silver	2.5	Aluminium	Middle Section	Subracks, Cases, Chassis
34562-814	220 mm	Silver	2.5	Aluminium	Middle Section	Subracks, Cases, Chassis
34562-815	280 mm	Silver	2.5	Aluminium	Middle Section	Subracks, Cases, Chassis
34562-816	340 mm	Silver	2.5	Aluminium	Middle Section	Subracks, Cases, Chassis
34562-822	1000 mm	Silver	2.5	Aluminium	Middle Section	Subracks, Cases, Chassis

ADDITIONAL PRODUCT DETAILS

Delivery may be in Standard Pack Quantity (SPQ). Pricing is per individual item.

One guide rail consists of 1 pair of head pieces and 1 profile piece.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE